## SV 102A+ Dual-Channel Acoustic Dosimeter



The SV102A+ is a Class 1 dual-channel noise dosimeter that has been designed for the accurate measurement of noise exposure to ISO 9612 and MIRE (microphone in real ear) measurements to ISO 11904-1.

This new instrument uses a class beating high resolution, full color OLED screen making it even easier to read; even in full daylight. The small memory capability of its predecessor; the SV 102A, has been upgraded by adding a microSD card for an incredible amount of storage capability. Also new is an LED that indicates the status of the measurement and changes color when the noise dose exceeds the limit set. A unique feature of all SVANTEK dosimeters, including the SV 102A+, is their ability to simultaneously analyze 1/1 octave and record audio events. The use of 1/1 octave analysis is the most accurate method for the correct selection of hearing protection to ISO 4869-2 while simultaneous audio recording allows the user to capture and eliminate false sounds affecting the result of exposure to noise.

Unlike classic single channel noise dosimeters, the two channel SV102A+ gives the unique opportunity to assess the exposure on both sides of the head simultaneously. This is particularly important

where a worker is exposed to noise coming from a dominant directional source where placing the microphone on only one side could understate the true level of noise exposure. Another use of dual channel technology is the simultaneous measurement of noise both outside and inside any hearing protection being used with the use of a SV 25S MIRE microphone.

MIRE methodology requires 1/3 octave analysis, another feature uniquely available in the SV102A+. MIRE measurement involves measuring the sound in the ear and performing a one-third octave band analysis on it. Using the SV102A+ in conjunction with a special microphone probe like the SV25S, placed at the entrance of the ear canal, makes this all possible. A typical application of MIRE measurement is noise exposure monitoring in telephone call centres where the sound comes from the headphones; an application not suited to classical dosimetry methods.

🗖 🔜 14:48

102

**& 011 4684 2232** 

Left ch. Right ch.

SLM & 4/3 Detaux

SVANTER

ര്ദ്ദ് www.siafa.com.ar

🖂 ventas@siafa.com.ai

🧐 SIAFA

LAF

#### **Features**

- Dual-channel acoustic dosimeter conforming to Class 1 IEC 61672
- Dual-channel measurement in accordance to ISO 9612
- Dual-channel MIRE measurement to ISO 11904-1
- Dual-channel 1/1 or 1/3 octave real-time analyser (option)
- Single measurement range 45 dBA RMS ÷ 141 dBA Peak
- MIRE measurement technique with optional SV 25S
- Three parallel independent profiles per channel
- Audio Events Recording to microSD card (option)
- Automatic calibration thanks to the TEDS technology
- USB interface
- OLED color display with super brightness and contrast
- Extremely compact, light weight (260 grams with batteries) and robust case (volume comparable to PDA devices)



# SV 102A+ Technical Specification



### Dosimeter/SLM/Analyser

Standards	_IEC 61252; ANSI S1.25-1991; Class 1: IEC 61672:2002, ISO 11904-1	
Acoustic Dosimeter Mode	Lav/Leq, SPL, Lmax, Lmin, SEL, SEL8, PSEL, LEPd, Dose (%),	
	TWA, E, E_8h, Peak, Run Time, Upper Limit Time (ULT),	
	L(C-A), Projected Dose (D_8h)	
SLM Mode	L <sub>eg</sub> , Spl, SEL, L <sub>EPd</sub> , L <sub>den</sub> , L <sub>tm3</sub> , L <sub>tm5</sub> , statistics - L <sub>n</sub> (L <sub>1</sub> - L <sub>99</sub> ), L <sub>Max</sub> , L <sub>Min</sub> , L <sub>Peak</sub>	
	Simultaneous measurement in three profiles with independent set of filters and detectors	
Weighting Filters	_A, C and Z	
RMS Detector	_Digital true RMS detector with Peak detection, resolution 0.1 dB	
	Time constants: Slow, Fast, Impulse	
Microphone	_SV 7052E, prepolarised, 1/2" housing	
	SV 25S, special microphone with dedicated probe for	
	Microphone-In-Real-Ear technique (option)	
Preamplifier	_SV 15 with integrated cable	
Measurement Range	_45 dBA RMS ÷ 141 dBA Peak (with SV 7052E microphone)	
Typical noise floor	less than 35 dBA	
Frequency Range	20 Hz ÷ 20 kHz, sampling rate 48 kHz	
Dynamic Range	100 dB	
Data Logger <sup>1</sup>	Time-history logging of Leq/Lmax/Lmin/Peak/Lav results to internal memory with	
	time step down to 100 millisecond to microSD card	
Audio Recorder <sup>1</sup>	Time-domain signal events recorder (option)	
Dual-channel Mode	_Dual-channel measurement mode with second microphone SV 7052E or SV 25S (option)	
1/1 Octave <sup>1</sup>	Dual-channel 1/1 octave real-time analysis and spectra logging,	
	10 filters with centre frequencies from 31.5 Hz to 16 kHz, Type 1: IEC 61260 (option)	
1/3 Octave <sup>1</sup>	Dual-channel 1/3 octave real-time analysis and spectra logging,	
	31 filters with centre frequencies from 20 Hz to 20 kHz, Type 1, IEC 61260 (option)	

#### **Basic Data**

Input	2 x LEMO 2-pin, Direct	
Display	Colour 160 x 128 pixels OLED type	
Memory	MicroSD card 4 GB (removable & upgradeable)	
Interfaces	USB 1.1 Client,	
	Extended I/O - AC output (1 V Peak) / Digital Outp	out (Alarm trigger) / Digital Input (Input trigger)
Power Supply	Two AA batteries (alkaline)	operation time > 16 h (3.0 V / 1.6 Ah) <sup>2</sup>
	Two rechargeable batteries (not included)	operation time > 20h (2.4 V / 2.6 Ah) <sup>2</sup>
	USB interface	150 mA HUB
Environmental Conditions	Temperature	from -10 °C to 50 °C
	Humidity	up to 90 % RH, non-condensed
Dimensions	95 x 83 x 33 mm (without microphones)	
Weight	260 grams with batteries (without microphones)	

<sup>1</sup>function parallel to the acoustic dosimeter mode or meter mode

<sup>2</sup>depends on instrument operation mode







Continuous product development and innovation are the policy of our company. Therefore, we reserve the right to change the specifications without prior notice.

#### SVANTEK Sp. z o. o.

ul. Strzygłowska 81, 04-872 WARSAW, POLAND phone/fax (+48) 22 51 88 320, (+48) 22 51 88 312 http://www.svantek.com e-mail: office@svantek.com.pl

### Higiene Ocupacional y Medio Ambiente ⊗ www.siafa.com.ar w ventas@siafa.com.ar 011 4684 2232